



humiSteam "Wellness"
Humidifier for steam baths

Electrode humidifier for wellness applications

The reliable and easy-to-install Carel solution complete with all the functions, accessories and controllers for steam bath applications.

- Operation in time bands at different temperature set points;
- Operation on mains water;
- External device management: 4 pumps (for essences and disinfection), 2 fans, 1 light;
- 12 sizes available from 1 to 65 kg / h;
- Drain pump to facilitate the removal of scale when draining the water.

humiSteam Wellness, part of the family of immersed electrode steam humidifiers, is designed for steam bath installations.

It is equipped with the "W" controller, complete with large graphic display, for centralised management of the various functions:

- Scheduled daily and weekly operation;
- Different temperature set points for different time bands;

- Up to 3 actuators for the distribution of essences, and 1 for the "disinfection" cycle;
- Up to 2 fans and interior light;
- The display-keypad unit can be detached from the humidifier and connected remotely, so as to facilitate integration into OEM products.



Active temperature probes

Essence control

Disinfection control



Reliability

Cylinders with snap-on power connectors for easy fast and risk-free maintenance



Ease of use

Backlit LCD display for clear understanding of the unit's operating status and diagnostics.



Hygiene

The water is automatically drained if the humidifier remains inactive for a certain period of time, avoiding stagnation.


The controller is based on pCO technology, one of the mainstays of the CAREL range, offering the following advantages:

- ease of use thanks to the graphic display with icons and messages in various languages;
- connectivity via the main protocols (Modbus®, BACnet™ and LON with

- external gateway);
- operating hour counter and alarm log management;
- easy software customisation for OEM applications;
- diagnostics with text messages and alarm log.

humiSteam uses mains water and manages the water concentration and foam formation completely automatically, to maximise efficiency. The CAREL range also includes:

- temperature probes (UEKNTC*; ASET*);
- steam pipes and nozzles.



Part number

U E _ _ _ W _ _ 0 1

steam production:

001= 1.5 kg/h
003= 3 kg/h
005= 5 kg/h
008= 8 kg/h
009= 9 kg/h
010= 10 kg/h
015= 15 kg/h
018= 18 kg/h
025= 25 kg/h
035= 35 kg/h
045= 45 kg/h
065= 65 kg/h

power supply:

D= 230 V 1~
K= 230 V 3~
L= 400 V 3~

options:

0 = standard cylinder
C= standard openable cylinder
1= cylinder for low conductivity
2= openable cylinder for low conductivity

NB: • not all combinations of part numbers are available;
• UEW: 230 V single-phase and three-phase, 400 V three-phase.

humiSteam table

Specifications	UE001*	UE003*	UE005*	UE008	UE009*	UE010*	UE015*	UE018*	UE025*	UE035*	UE045*	UE065*
General												
Rated steam production - kg/h	1.5	3	5	8	9	10	15	18	25	35	45	65
Power consumption - kW	1.12	2.25	3.75	6.00	6.75	7.50	11.25	13.5	18.75	26.25	33.75	48.75
Power supply for "Wellness" models • 230 Vac 50/60 Hz single-phase • 230 Vac 50/60 Hz three-phase • 400 Vac 50/60 Hz three-phase	●	● ● ●	● ● ●	● ●	●	● ●	● ●	●	●	●	●	●
Steam connection - mm	Ø 22/30		Ø 30						Ø 40		Ø 2x40	
Operating conditions	-1T40°C, 10-90% rH non-condensing											
Storage conditions	-10T70°C, 5-95% rH non-condensing											
Water fill												
Connection	3/4" G male											
Instant flow rate - l/m	0.6	0.6	0.6	0.6	1.1	1.1	1.1	1.1	5.85	5.85	5.85	7
Conductivity limits - µS/cm (*)	75 to 1250											
Water drain												
Connection	Ø 40											
Instant flow rate - l/m	7 (50 Hz) - 9 (60 Hz)								17.5 (50 Hz); 22.5 (60 Hz)			

● available

Headquarters

CAREL INDUSTRIES HQs
Via dell'Industria, 11
35020 Brugine - Padova (Italy)
carel@carel.com



HygroMatik GmbH

Lise-Meitner-Straße 3
24558 Henstedt-Ulzburg - Germany
hy@hygromatik.de

RECUPERATOR

Via Valfurva 13
20027 Rescaldina (MI), Italy
customercare@recuperator.eu

ENGINIA S.r.l.

Viale Lombardia, 78
20056 Trezzo Sull'Adda (MI), Italy
commerciale@enginiasrl.com

For more information

CAREL Asia - www.carel.hk
CAREL Australia - www.carel.com.au
CAREL Central & Southern Europe - www.carel.com
CAREL Czech & Slovakia - www.carel.cz
CAREL spol. s.r.o.
CAREL Deutschland - www.carel.de
CAREL China - www.carel-china.com
CAREL France - www.carelfrence.fr
CAREL Ibérica - www.carel.es
CAREL Ireland - www.carel.ie
FarrahVale Controls & Electronics Ltd.
CAREL Italy - www.carel.it
CAREL India - www.carel.in
CAREL Japan - www.carel-japan.com
CAREL Nordic - www.carelnordic.se
CAREL U.K. - www.careluk.com
CAREL U.S.A. - www.carelusa.com CAREL

Authorized distributor



Umecto AB – del av Klimatbyrån AB
Tel: +46 (0)10-288 92 90
info@umecto.se | www.umecto.se
Sverige | Sweden

CAREL

To the best of CAREL INDUSTRIES S.p.A. knowledge and belief, the information contained herein is accurate and reliable as of the date of publication. However, CAREL INDUSTRIES S.p.A. does not assume any liability whatsoever for the accuracy and completeness of the information presented without guarantee or responsibility of any kind and makes no representation or warranty, either expressed or implied. A number of factors may affect the performance of any products used in conjunction with user's materials all of which must be taken into account by the user in producing or using the products. The user should not assume that all necessary data for the proper evaluation of these products are contained herein and is responsible for the appropriate, safe and legal use, processing and handling of CAREL's products. The Information provided herein does not relieve the user from the responsibility of carrying out its own tests, and the user assumes all risks and liabilities related to the use of the products and/or information contained herein. © 2022 CAREL INDUSTRIES S.p.A. All rights reserved.